

ASMD030F-2 Product Details



ASMD030F-2
(ASMD050F-2)

TE Internal Number: RF1631-000

 [Active](#)

PolySwitch Resettable Devices

 [Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)


Product Highlights:

- Automotive, Surface Mount Application
- Vmax Operating = 60 V
- Imax = 10 A
- Family Name = ASMD
- Surface Mount Construction

[View all Features](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

 [Add to My Part List](#)
 [Request Sample](#)
 [Find Similar Products](#)
 [Buy Product](#)

Documentation & Additional Information

Product Drawings:

- None Available

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- [ASMD030F](#) (PDF, English)

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Electrical Characteristics:

- [Vmax Operating \(V\)](#) = 60
- [Imax \(A\)](#) = 10
- [IH \(Room Temperature\) \(A\)](#) = 0.23
- [IT \(Room Temperature\) \(A\)](#) = 0.59
- [Rmin \(Ω\)](#) = 0.98
- [R1 Max \[Post Trip\] \(Ω\)](#) = 4.80
- Power Dissipation (Typical) (W) = 1.10

Termination Related Features:

- Construction = Surface Mount

Contact Related Features:

- [Family Name](#) = ASMD

Configuration Related Features:

- [Form Factor \(inches\)](#) = 2920
- [Form Factor \(mm\)](#) = 7555

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Reflow solder capable to 245°C, Reflow solder capable to 260°C
- RoHS/ELV Compliance History = Always was RoHS compliant

Conditions for Usage:

- [Operating Temperature \(Max.\) \(°C\)](#) = 85

Operation/Application:

- Application = Automotive, Surface Mount

Packaging Related Features:

- Packaging Method = Tape & Reel

Other:

- Brand = Raychem

 [BOOKMARK](#) 

Corporate Information

[Who We Are](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)

Quick Links

[Check Distributor Inventory](#)
[Cross Reference](#)
[Find Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

Customer Support

[Email or Chat with Us](#)
[Find a Phone Number](#)
[Search Knowledge Base](#)
[Manage Your Account](#)

Sign up for our eNewsletter

Enter your email address

Follow Us On:



Visit Us On:

