



PRODUCTS & SERVICES:

Switches >

Indicator Lights >

Connectors >

Defense/Aerospace
Connectors >

Contract
Manufacturing >

Custom Assembly >

Custom Switches and
Connectors >



Search Catalog

By Keyword

All Categories Socket Connectors

[All Categories](#) > [Connectors](#) > [Insulation Displacement Connectors - Commercial & MIL SPEC](#) > [Insulation Displacement Connectors - Commercial](#) > [Socket Connectors](#) > Item # CWR-217-16-0000

[Download PDF](#) [Printable Page](#) [Email This Page](#) [Save To Favorites](#)

Request Information

Item # CWR-217-16-0000, Socket Connectors



[larger image](#)

MORE IMAGES

- Features of Socket Connectors
- Socket Connectors with Metal Strain Relief Strap
- Socket Connectors with Non-Strain Relief Cover
- Contact Drawing for Socket Connectors
- Polarization Drawing of Socket Connectors
- Polarization Method Drawing of Socket Connectors
- How to Order Socket Cable Assemblies

DOWNLOADS

Dim Dwg CWR-217-XX-0000 (PDF, 579KB)

Plastic Key for Socket Connectors



[Plastic Key for Socket Connector](#)

[Check Distributor Stock](#) · [Specifications](#)

Check Distributor Stock

Check Distributor Stock [DIGI-KEY](#) [MOUSER](#)

Specifications

Style	IDC
Connector Type	Socket
Mounting	With Strain Relief
Plating	10µ in. Gold Over 50µ in. Nickel
Polarization	Central Polarizing Bump
Number of Contacts	16
Contacts	Phosphor Bronze Standard
Insulator Material	UL 94V-0 Flame Retardant Thermoplastic
Strain Relief Strap Material	Insulated Stainless Steel
Color	Blue
Operating Temperature	-55 to +125 °C
Maximum Current Rating (Per Contact)	1 A
Dielectric Withstand Voltage	Greater Than 500 VDC at Sea Level
Insulation Resistance	Greater Than 5 x 10 ⁹ ohms
Typical Withdrawal Force	2-8 oz/contact
Minimum Cover Pull-Off Force (Force Along Contacts Primary Axes)	8 oz/contact
Listing Agency (Consult drawing or factory for specific rating) ¹	Listed Agencies
Compliance	

¹ Due to ongoing advancements, additional agency certifications may be available, contact us for more information.

Request Information

CW INDUSTRIES

130 James Way - Southampton, PA 18966

215-355-7080 | fax: 215-355-1088 | info@cwind.com

[Legal](#) | [Sitemap](#) | [Catalog Index](#)

© 2011 CW Industries - All Rights Reserved