



PRODUCTS & SERVICES:

Switches ▶

Indicator Lights ▶

Connectors ▶

Defense/Aerospace  
Connectors ▶

Contract  
Manufacturing ▶

Custom Assembly ▶

Custom Switches and  
Connectors ▶



Search Catalog

By Keyword

All Categories  Socket Connectors

[All Categories](#) > [Connectors](#) > [Insulation Displacement Connectors - Commercial & MIL SPEC](#) > [Insulation Displacement Connectors - Commercial](#) > [Socket Connectors](#) > Item # CWR-217-26-0203

[Download PDF](#) [Printable Page](#) [Email This Page](#) [Save To Favorites](#)

Request Information

Item # CWR-217-26-0203, Socket Connectors



[larger image](#)

[Check Distributor Stock](#) · [Specifications](#)

Check Distributor Stock

Check Distributor Stock

Specifications

Style	IDC
Connector Type	Socket
Mounting	With Strain Relief
Plating	Tin
Polarization	Central Polarizing Bump
Number of Contacts	26
Contacts	Phosphor Bronze Standard
Insulator Material	UL 94V-0 Flame Retardant Thermoplastic
Strain Relief Strap Material	Insulated Stainless Steel
Color	Blue
Operating Temperature	-55 to +125 °C
Maximum Current Rating (Per Contact)	1 A
Dielectric Withstand Voltage	Greater Than 500 VDC at Sea Level
Insulation Resistance	Greater Than 5 x 10 <sup>9</sup> ohms
Typical Withdrawal Force	2-8 oz/contact
Minimum Cover Pull-Off Force (Force Along Contacts Primary Axes)	8 oz/contact
Compliance	

Request Information

MORE IMAGES

- Features of Socket Connectors
- Socket Connectors with Metal Strain Relief Strap
- Socket Connectors with Non-Strain Relief Cover
- Contact Drawing for Socket Connectors
- Polarization Drawing of Socket Connectors
- Polarization Method Drawing of Socket Connectors
- How to Order Socket Cable Assemblies

DOWNLOADS

Dim Dwg CWR-217-XX-0203 (PDF, 581KB)

Plastic Key for Socket Connectors



[Plastic Key for Socket Connector](#)