



G98-0075-XX

ORIGINAL EN ROUGE

MATIERE: Acier inoxydable
PROTECTION: Passivation

h	26-06-12	Ajout T11 (DLG319.12)
g	09-12-04	OE121204
f	16-05-02	Ajout T02 (DLG342.02)
e	07-01-02	Ajout T09
d	17-09-01	Ajout T16
c	29-09-99	Extension cotilles DL 1131.1132.99 OE630999
b	11-05-99	Extension cotilles DL 626-627-628.99
a	27-03-96	MIS R53000

ORIGINE : DEQ2019B

DESIGNATION : SE ACCESSOIRE DROIT INOX P/N: 698-0075-XX

SERIE 983 DATE 16 02 96

REF : VISA Creation 12/02/96 VISA Approbation

To	Le	Sortie	Ind	Filet	A	B	C	D	E	F	G	Ref	Turbomeca	Ref	Operatoire
0	1-2-20	uif	28	19.27	37.2	8.5	4.9	7	8.5	31	9947801601	001			
1	1-2-20	uif	28	19.27	37.2	8.5	6.2	8.3	9.5	51	9947801602	001			
03	5-8-24	uif	28	22.24	37.2	8.5	4.9	7	8.5	51	9947801601	001			
04	5-8-24	uif	28	22.24	37.2	8.5	8.2	10.3	11.8	51	9947801602	001			
05	5-8-24	uif	28	22.24	37.2	8.5	8.6	10.7	12.5	51	9947801603	001			
06	3-4-20	uif	28	25.39	37.2	8.5	8.6	10.7	12.5	51	9947801202	001			
07	3-4-20	uif	28	25.39	44.2	15.5	9.6	12.7	14.5	51	9947801202	001			
08	3-4-20	uif	28	25.39	44.2	15.5	12.98	16.2	16.5	51	9947801203	001			
09	7-8-20	uif	28	28.59	44.2	15.5	13.1	16.2	17.3	51	9947801401	001			
10	1-20	uif	28	31.84	44.2	15.5	13.1	16.2	18	51	9947801601	001			
11	1-16-18	uif	28	34.54	44.2	15.5	13.1	16.2	18	51	9947801601	001			
12	1-16-18	uif	28	34.54	44.2	15.5	16.6	19.7	21.5	51	9947801602	001			
13	3-16-18	uif	28	37.76	44.2	15.5	16.6	19.7	21.5	51	9947801601	001			
14	3-16-18	uif	28	37.76	44.2	15.5	19.4	22.5	24.5	51	9947802602	001			
15	3-16-18	uif	28	40.69	44.2	15.5	16.6	19.7	21.5	51	9947802201	001			
16	3-16-18	uif	28	40.69	44.2	15.5	19.4	22.5	24.5	51	9947802202	001			
17	3-16-18	uif	28	40.69	44.2	15.5	22.4	25.5	27.5	51	9947802203	001			
18	3-16-18	uif	28	44.06	44.2	15.5	22.4	25.5	27.5	51	9947802401	001			



Connecteurs Electriques Deutsch
17, rue LAVOISIER - BP 117 - 27091 EPREUX CEDEX 9 - FRANCE

TECHNICAL DATA SHEET

204-19-A/F00