

DTS20W23-35PN [V001] ✓ ACTIVE

TE Internal #: YDTS20W23-35PNV001

TE Internal Description: RECP ASSY

Mil-Spec: [D38999/20WH35PN]

D38999: Square Flange, 23-35 insert

[View on TE.com >](#)



All D38999: Square Flange, 23-35 insert (4)

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2024 (240) SVHC > Threshold: Pb (1.2% in Copper Alloy) Cd (4.32% in Plating) Article Safe Usage Statements: Use personal protective equipment as required. Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-D38999-DTS24M
D38999: Straight Plug, 23-35 Insert

Customers Also Bought



TE Part #CN9930-000
SBP190319WE2.5



TE Part #CAT-T3437-T548
TMS-SCE Military Grade Sleeves



TE Part #66565-7
III+ SKT,24-20,TIN,LP



TE Part #205165-1
RECEPT ASSY,25 POSN,AMPLIMITE



TE Part #213864-1
23-37 RCPT HSG,REV SEX,CPC



TE Part #2-967642-1
3POS MQS REC SEALED COD B



TE Part #1617163-7
JMACDD-26XM = M39016/20-054M



TE Part #6116173-1
INV MJ.1X1,PNL GRD,SHLD,LED (G/Y)