

# DTS26W11-99SN [V001] ✓ ACTIVE

TE Internal #: YDTS26W11-99SNV001

TE Internal Description: PLUG ASSY

Mil-Spec: [D38999/26WB99SN]

[View on TE.com >](#)



## Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) SVHC > Threshold: Cd (100% in 10563731072) Pb (3.5% in 74024568) <b>Article Safe Usage Statements:</b> Use personal protective equipment as required. Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts



TE Part # CAT-D38999-DTS14X  
Jam Nut: D38999, 11-99 Insert



TE Part # CAT-D38999-DTS6E  
D38999: Square Flange, 11-99 insert


## Customers Also Bought



TE Part # YDTS26W17-99PNV001  
PLUG ASSY



TE Part # CON SMA018-4-G  
SMA Jack 50 Ohm Panel Mount




TE Part # CAT-R21-731072  
Bulbous Heat Shrink Boots: Lipped,  
Straight



TE Part # 323061  
TERMINAL, SOLIS R HR 12-10 8



TE Part # 323063  
TERMINAL, SOLIS R HR 12-10 1/4



TE Part # 5-1617791-1  
FCA-125-3702L=M83536/37-002L



TE Part # 1982299-2  
ELCON MINI 2P CABLE CONN, WITH  
CODING(L)



TE Part # YDTS26W23-21PNV001  
PLUG ASSY



TE Part # YDTS26W11-35SBV001  
PLUG ASSY

## Documents

### Datasheets & Catalog Pages

[DEUTSCH DTS Series Connectors for 38999 QRG](#)

English