

Part Number: **5501004F**

General Description	
Series	550
Configuration	5 mm Lens
Description	5 mm Blue Non - Diffused Water Clear CBI Right Angle B
Package Options	Bulk Packaging
Sizes	5mm
Lamp Type	Single Color
Viewing	Top View
Polarity	Cathode Right
Lens Style	Non - Diffused

Absolute Maximum Ratings (Ta = 25Â°)	
Solder Temperature	260Â° for 5 sec
Operating Temperature	- 40 to +80
Storage Temperature	- 40 to +100

Operating Characteristics	
Color	Blue
LED Type	High Efficiency
Luminous Intensity Min	520
Luminous Intensity Typical	1000
Luminous Intensity Max	1500
Test Current mA	20mA
Emitted Color	Blue
Power Dissipation Max	120mW



5501004F

check stock



[This is a
RoHS Compliant Product
To learn more click here](#)