

[Home](#) > [5510607100F](#)

Search For Part Number

Part Number: **5510607100F**

General Description

Series	551
Configuration	3 mm Lens
Description	3 mm CBI Right Angle
Package Options	Bulk Packaging
Sizes	3mm
Lamp Type	Single Housing
Viewing	Right Angle
Polarity	Cathode Right
Lens Style	Tinted, Diffused
Viewing Angle	60
LED Centerline	5.0mm

Absolute Maximum Ratings (Ta = 25Â°)

Reverse Current	100 @ Vr = 5V
Derating	0.086 (mA/degC)
Reverse Voltage	5
Solder Temperature	260 for 5 secs
Operating Temperature	-40 to +85
Storage Temperature	-55 to +100

Operating Characteristics

Color	Green
LED Type	Integral Resistor
Peak Wave Length	565
Luminous Intensity Min	5.6
Luminous Intensity Typical	19
Forward Voltage Typical	10
Forward Voltage Max	20
Test Current mA	20mA



5510607100F

[check stock](#)



[This is a
RoHS Compliant Product.
To learn more click here.](#)