

[Home](#) > [5511307100F](#)

Search For

Part Number: **5511307100F**

General Description

Series	551
Configuration	3 mm Lens
Description	3 mm CBI Right Angle
Package Options	Bulk Packaging
Sizes	3mm
Lamp Type	Single Housing
Viewing	Right Angle
Polarity	Cathode Right
Lens Style	Tinted, Diffused
Viewing Angle	60
LED Centerline	5.0mm

Absolute Maximum Ratings (Ta = 25Â°)

Reverse Current	10 @ Vr = 5V
Reverse Voltage	5
Solder Temperature	260 for 5 secs
Operating Temperature	-55 to +100
Storage Temperature	-55 to +100

Operating Characteristics

Color	Green
LED Type	Low Current
Peak Wave Length	565
Luminous Intensity Min	1
Luminous Intensity Typical	1.6
Forward Voltage Typical	1.9
Forward Voltage Max	2.2
Test Current mA	20mA
Power Dissipation Max	20mW



5511307100F

[check stock](#)



[This is a
RoHS Compliant Product.
To learn more click here.](#)