

[Home](#) > [5530132300F](#)

Search For

Part Number: **5530132300F**

| General Description | |
|---------------------|--------------------|
| Series | 553 |
| Configuration | 3 mm Lens |
| Description | 3 mm Bi -Level CBI |
| Package Options | Bulk Packaging |
| Sizes | 3mm |
| Lamp Type | Bi-Level Housing |
| Viewing | Right Angle |
| Polarity | Cathode Right |
| Lens Style | Tinted, Diffused |
| Viewing Angle | 45 |
| LED Centerline | 2.54mm |

| Absolute Maximum Ratings (Ta = 25Â°) | |
|--------------------------------------|----------------|
| Solder Temperature | 260 for 5 secs |
| Operating Temperature | -25 to +85 |
| Storage Temperature | -30 to +100 |

| Operating Characteristics | | |
|----------------------------|-----------------|-----------------|
| | LED Position: 1 | LED Position: 2 |
| Color | Yellow | Green |
| LED Type | High Efficiency | High Efficiency |
| Peak Wave Length | 585 | 563 |
| Luminous Intensity Min | 2.2 | 5.6 |
| Luminous Intensity Typical | 6.3 | 16 |
| Forward Voltage Typical | 2.1 | 2.1 |
| Forward Voltage Max | 3 | 3 |
| Power Dissipation Max | 60mW | 75mW |



5530132300F

[check stock](#)



[This is a RoHS Compliant Product](#)
[To learn more click here](#)