

[Home](#) > [5530112200F](#)

Search For

Part Number: **5530112200F**

General Description	
Series	553
Configuration	3 mm Lens
Description	3 mm Bi -Level CBI
Package Options	Bulk Packaging
Sizes	3mm
Lamp Type	Bi-Level Housing
Viewing	Right Angle
Polarity	Cathode Left
Lens Style	Tinted, Diffused
Viewing Angle	60
LED Centerline	2.54mm

Absolute Maximum Ratings (Ta = 25°C)	
Solder Temperature	260 for 5 secs
Operating Temperature	-55 to +100
Storage Temperature	-55 to +100

Operating Characteristics		
	LED Position: 1	LED Position: 2
Color	Red	Green
LED Type	Standard Efficiency	Standard Efficiency
Peak Wave Length	635	565
Luminous Intensity Min	7.4	4.7
Luminous Intensity Typical	10	12.6
Forward Voltage Typical	2	2.1
Forward Voltage Max	2.8	2.8
Power Dissipation Max	100mW	100mW



5530112200F

[check stock](#)



[This is a RoHS Compliant Product](#)
[To learn more click here](#)