

[Home](#) > [5530112306F](#)

Search For

Part Number: **5530112306F**

General Description	
Series	553
Configuration	3 mm Lens
Description	3 mm Bi -Level CBI
Package Options	Bulk Packaging
Sizes	3mm
Lamp Type	Bi-Level Housing
Viewing	Right Angle
Polarity	Cathode Right
Lens Style	Tinted, Diffused
Viewing Angle	45
LED Centerline	2.54mm

Absolute Maximum Ratings (Ta = 25Â°)	
Solder Temperature	260 for 5 secs
Operating Temperature	-25 to +85
Storage Temperature	-30 to +100

Operating Characteristics		
	LED Position: 1	LED Position: 2
Color	Red	Green
LED Type	High Efficiency	High Efficiency
Peak Wave Length	650	563
Luminous Intensity Min	3.6	5.6
Luminous Intensity Typical	10	16
Forward Voltage Typical	2	2.1
Forward Voltage Max	3	3
Power Dissipation Max	60mW	75mW



5530112306F

[check stock](#)



[This is a RoHS Compliant Product](#)
[To learn more click here](#)