

[Home](#) > [5530132400F](#)

Search For

Part Number: **5530132400F**

General Description	
Series	553
Configuration	3 mm Lens
Description	3 mm Bi -Level CBI
Package Options	Bulk Packaging
Sizes	3mm
Lamp Type	Bi-Level Housing
Viewing	Right Angle
Polarity	Cathode Left
Lens Style	Tinted, Diffused
Viewing Angle	60
LED Centerline	2.54mm

Absolute Maximum Ratings (Ta = 25°C)	
Solder Temperature	260 for 5 secs
Operating Temperature	-55 to +100
Storage Temperature	-55 to +100

Operating Characteristics		
	LED Position: 1	LED Position: 2
Color	Green	Yellow
LED Type	Standard Efficiency	Standard Efficiency
Peak Wave Length	565	585
Luminous Intensity Min	4.7	7.4
Luminous Intensity Typical	12.6	10
Forward Voltage Typical	2.1	2.1
Forward Voltage Max	2.8	2.8
Power Dissipation Max	100mW	60mW



5530132400F

[check stock](#)



[This is a RoHS Compliant Product](#)
[To learn more click here](#)