

Part Number: **5530233004F**

General Description	
Series	553
Configuration	3 mm Lens
Description	3 mm Bi -Level CBI
Package Options	Bulk Packaging
Sizes	3mm
Lamp Type	Bi-Level Housing
Viewing	Right Angle
Polarity	Cathode Right
Lens Style	Tinted, Diffused
Viewing Angle	60
LED Centerline	5.0mm

Absolute Maximum Ratings (Ta = 25Å °)	
Reverse Current	100 @ Vr = 5V
Reverse Voltage	5
Solder Temperature	260 for 5 secs
Operating Temperature	-40 to +100
Storage Temperature	-55 to +100

Operating Characteristics	
Color	Yellow
LED Type	Low Current
Peak Wave Length	591
LED Position	1,2
Luminous Intensity Min	2.3
Luminous Intensity Typical	5
Forward Voltage Typical	1.8
Forward Voltage Max	2.4
Test Current mA	20mA
Power Dissipation Max	75mW



[553 -xxxx -xxx PDF](#)

[check stock](#)



This is a [RoHS Compliant Product](#).
[To learn more click here](#)