

[Home](#) > [5530313300F](#)

Search For Part Number

Part Number: **5530313300F**

General Description	
Series	553
Configuration	3 mm Lens
Description	3 mm Bi -Level CBI
Package Options	Bulk Packaging
Sizes	3mm
Lamp Type	Bi-Level Housing
Viewing	Right Angle
Polarity	Cathode Right
Lens Style	Tinted, Diffused
Viewing Angle	60
LED Centerline	2.54mm

Absolute Maximum Ratings (Ta = 25Â°)	
Solder Temperature	260 for 5 secs
Operating Temperature	-40 to +85
Storage Temperature	-55 to +100

Operating Characteristics		
	LED Position: 1	LED Position: 2
Color	Red	Yellow
LED Type	Integral Resistor	Integral Resistor
Peak Wave Length	635	585
Luminous Intensity Min	8.7	3.7
Luminous Intensity Typical	29	12.6
Forward Voltage Typical	10	10
Forward Voltage Max	20	20



5530313300F

[check stock](#)



[This is a RoHS Compliant Product](#)
[To learn more click here](#)