

Part Number: **5615801080F**

General Description	
Color	Amber
Series	561
Configuration	5 mm Lens
Description	5 mm Stand -Off 0.800" Amb WC
Package Options	Bulk Packaging
Sizes	5mm
Lamp Type	Single Color
Viewing	Top View
Polarity	Cathode Right
Lens Style	Non - Diffused

Absolute Maximum Ratings (Ta = 25°C)	
Solder Temperature	260°C for 5 sec
Operating Temperature	-30 to +100
Storage Temperature	-30 to +100

Operating Characteristics	
Color	Amber
LED Type	High Efficiency
Luminous Intensity Min	60
Luminous Intensity Typical	90
Test Current mA	20mA
Emitted Color	Amber
Power Dissipation Max	125mW



5615801080F

[check stock](#)



[This is a RoHS Compliant Product](#)
[To learn more click here](#)