

Part Number: **5642210222F**

General Description

Series	564
Configuration	3 mm Lens
Description	3 mm Green/Green/Green Backlighting Tri -Level CBI Non - Diffused
Package Options	Bulk Packaging
Sizes	3mm
Lamp Type	Tri -Level Housing
Viewing	Right Angle
Polarity	Cathode Right
Lens Style	Tinted, Non -Diffused
Viewing Angle	45
LED Centerline	5.0mm

Absolute Maximum Ratings (Ta = 25Å °)

Reverse Current	100 @ Vr = 5V
Derating	0.4 (mA/degC)
Solder Temperature	260 for 5 secs
Operating Temperature	-55 to +100
Storage Temperature	-55 to +100

Operating Characteristics

Color	Green
LED Type	Low Current
Peak Wave Length	565
LED Position	1,2,3
Luminous Intensity Min	32
Luminous Intensity Typical	50
Forward Voltage Typical	2.1
Forward Voltage Max	2.8
Test Current mA	20mA
Power Dissipation Max	100mW



5642210222F

[check stock](#)



[This is a RoHS Compliant Product](#)
[To learn more click here](#)