

Part Number: **5680213333F**

General Description	
Series	568
Configuration	3 mm Lens
Description	3 mm Quad -Level Backlighting CBI Y -Y-Y-Y
Package Options	Bulk Packaging
Sizes	3mm
Lamp Type	Quad Level Housing
Viewing	Right Angle
Polarity	Cathode Right
Lens Style	Tinted, Diffused
Viewing Angle	60
LED Centerline	5.0mm

Absolute Maximum Ratings (Ta = 25Å °)	
Reverse Current	100 @ Vr = 5V
Reverse Voltage	5
Solder Temperature	260 for 5 secs
Operating Temperature	-40 to +100
Storage Temperature	-55 to +100

Operating Characteristics	
Color	Yellow
LED Type	High Efficiency
Peak Wave Length	591
LED Position	1-4
Luminous Intensity Min	2.3
Luminous Intensity Typical	5
Forward Voltage Typical	1.8
Forward Voltage Max	2.4
Test Current mA	20mA
Power Dissipation Max	75mW



5680213333F

[check stock](#)



[This is a RoHS Compliant Product](#)
[To learn more click here](#)