

[Home](#) > [5682211122F](#)

Search For Part Number

Part Number: **5682211122F**

General Description

Series	568
Configuration	3 mm Lens
Description	3 mm Backlighting Quad-Level CBI R-R-G-G
Package Options	Bulk Packaging
Sizes	3mm
Lamp Type	Quad Level Housing
Viewing	Right Angle
Polarity	Cathode Right
Lens Style	Tinted, Non-Diffused
Viewing Angle	45
LED Centerline	2.54mm

Absolute Maximum Ratings (Ta = 25)

Solder Temperature	260 for 5 secs
Operating Temperature	-55 to +100
Storage Temperature	-55 to +100

Operating Characteristics

	LED Position: 1,2	LED Position: 3,4
Color	Red	Green
LED Type	High Efficiency	High Efficiency
Peak Wave Length	635	565
Luminous Intensity Min	8.7	32
Luminous Intensity Typical	29	50
Forward Voltage Typical	2	2.1
Forward Voltage Max	2.8	2.8
Power Dissipation Max	100mW	100mW



5682211122F

[check stock](#)



This is a
[RoHS Compliant Product](#)
[To learn more click here](#)