

[Home](#) > [5682213292F](#)

Search For

Part Number: **5682213292F**

General Description	
Series	568
Configuration	3 mm Lens
Description	3 mm Backlighting Quad -Level CBI Y -G-B-G
Package Options	Bulk Packaging
Sizes	3mm
Lamp Type	Quad Level Housing
Viewing	Right Angle
Polarity	Cathode Right
Lens Style	Tinted, Non -Diffused
Viewing Angle	45
LED Centerline	2.54mm

Absolute Maximum Ratings (Ta = 25Â°)	
Solder Temperature	260 for 5 secs
Operating Temperature	-55 to +100
Storage Temperature	-55 to +100

Operating Characteristics			
	LED Position: 1	LED Position: 2,4	LED Position: 3
Color	Yellow	Green	Blue
LED Type	High Efficiency	High Efficiency	High Efficiency
Peak Wave Length	585	565	470
Luminous Intensity Min	10	32	110
Luminous Intensity Typical	29	50	
Forward Voltage Typical	2.1	2.1	3.5
Forward Voltage Max	2.8	2.8	4
Power Dissipation Max	60mW	100mW	90mW



5682213292F

[check stock](#)



[This is a RoHS Compliant Product](#)
[To learn more click here](#)