

Part Number: 5682231111F

General Description	
Series	568
Configuration	3 mm Lens
Description	3 mm Backlighting Quad -Level CBI R -R-R-R
Package Options	Bulk Packaging
Sizes	3mm
Lamp Type	Quad Level Housing
Viewing	Right Angle
Polarity	Cathode Right
Lens Style	Tinted, Non -Diffused
Viewing Angle	45
LED Centerline	5.0mm

Absolute Maximum Ratings (Ta = 25Â°)	
Derating	0.4 (mA/degC)
Reverse Voltage	5
Solder Temperature	260 for 5 secs
Operating Temperature	-55 to +100
Storage Temperature	-55 to +100

Operating Characteristics	
Color	Red
LED Type	High Efficiency
Peak Wave Length	635
LED Position	1-4
Luminous Intensity Min	8.7
Luminous Intensity Typical	29
Forward Voltage Typical	2
Forward Voltage Max	2.8
Test Current mA	20mA
Power Dissipation Max	100mW



5682231111F

check stock



This is a
RoHS Compliant Product
To learn more click here