

[Home](#) > [5682232222F](#)

Search For  Part Number

Part Number: **5682232222F**

#### General Description

Series	568
Configuration	3 mm Lens
Description	3 mm Quad Backlighting G-G-G-G
Package Options	Bulk Packaging
Sizes	3mm
Lamp Type	Quad Level Housing
Viewing	Right Angle
Polarity	Cathode Right
Lens Style	Tinted, Non-Diffused
Viewing Angle	45
LED Centerline	5.0mm

#### Absolute Maximum Ratings (Ta = 25 )

Reverse Current	100 @ Vr = 5V
Derating	0.4 (mA/degC)
Solder Temperature	260 for 5 secs
Operating Temperature	-55 to +100
Storage Temperature	-55 to +100

#### Operating Characteristics

Color	Green
LED Type	High Efficiency
Peak Wave Length	565
LED Position	1-4
Luminous Intensity Min	32
Luminous Intensity Typical	50
Forward Voltage Typical	2.1
Forward Voltage Max	2.8
Test Current mA	20mA
Power Dissipation Max	100mW



5682232222F

[check stock](#)



[This is a  
RoHS Compliant Product  
To learn more click here](#)