

[Home](#) > [5710110F](#)

Search For  Part Number

Part Number: **5710110F**

General Description	
Series	571
Configuration	2 mm Lens
Description	2 mm Bi -Level CBI R -X
Package Options	Bulk Packaging
Sizes	2mm
Lamp Type	Bi-Level Housing
Viewing	Right Angle
Polarity	Cathode Pin 1 & 3
Lens Style	Tinted, Diffused
Viewing Angle	70
LED Centerline	2.54mm
Solder Temperature	260 for 5 secs

Absolute Maximum Ratings (Ta = 25Å °)	
Operating Temperature	-40 to +85
Storage Temperature	-40 to +85

Operating Characteristics		
	LED Position: 1	LED Position: 2
Color	Red	Blank
LED Type	Standard Efficiency	Standard Efficiency
Peak Wave Length	627	
Luminous Intensity Min	8	
Luminous Intensity Typical	15	
Forward Voltage Typical	2	
Forward Voltage Max	2.5	
Power Dissipation Max	105mW	



5710110F

[check stock](#)



[This is a  
RoHS Compliant Product  
To learn more click here](#)