

[Home](#) > [5710120F](#)

Search For Part Number

Part Number: **5710120F**

General Description

Series	571
Configuration	2 mm Lens
Description	2 mm Bi -Level CBI G -X
Package Options	Bulk Packaging
Sizes	2mm
Lamp Type	Bi-Level Housing
Viewing	Right Angle
Polarity	Cathode Pin 1 & 3
Lens Style	Tinted, Diffused
Viewing Angle	70
LED Centerline	2.54mm
Solder Temperature	260 for 5 secs

Absolute Maximum Ratings (Ta = 25Å °)

Operating Temperature	-40 to +85
Storage Temperature	-40 to +85

Operating Characteristics

	LED Position: 1	LED Position: 2
Color	Green	Blank
LED Type	Standard Efficiency	Standard Efficiency
Peak Wave Length	565	
Luminous Intensity Min	5	
Luminous Intensity Typical	10	
Forward Voltage Typical	2.2	
Forward Voltage Max	2.5	
Power Dissipation Max	105mW	



5710120F

[check stock](#)



[This is a
RoHS Compliant Product](#)
[To learn more click here](#)