

[Home](#) > [5710123104F](#)

Search For

Part Number: **5710123104F**

General Description	
Series	571
Configuration	2 mm Lens
Description	2 mm Bi -Level CBI G -Y
Package Options	Bulk Packaging
Sizes	2mm
Lamp Type	Bi-Level Housing
Viewing	Right Angle
Polarity	Cathode Pin 1 & 3
Lens Style	Tinted, Diffused
Viewing Angle	70
LED Centerline	2.54mm
Solder Temperature	260 for 5 secs

Absolute Maximum Ratings (Ta = 25Â°)	
Operating Temperature	-40 to +85
Storage Temperature	-40 to +85

Operating Characteristics		
	LED Position: 1	LED Position: 2
Color	Green	Yellow
LED Type	Standard Efficiency	Standard Efficiency
Peak Wave Length	565	590
Luminous Intensity Min	5	5
Luminous Intensity Typical	10	8
Forward Voltage Typical	2.2	2.1
Forward Voltage Max	2.5	2.5
Power Dissipation Max	105mW	105mW



5710123104F

[check stock](#)



[This is a RoHS Compliant Product](#)
[To learn more click here](#)