

[Home](#) > [5973211602F](#)

Search For

Part Number: **5973211602F**

General Description	
Series	597
Configuration	PLCC-2
Description	SMD LED PLCC2 O Sample Strip
Package Options	Sample Strip
Lamp Type	Single Color
LED Type	GaP
Lens Color	Non - Diffused

Absolute Maximum Ratings (Ta = 25°C)	
Forward Current mA	30mA
Derating	from 50°C @ .6mA/°C
Solder Temperature	260°C for 5 sec
Operating Temperature	-55~+100
Storage Temperature	-55~+100

Operating Characteristics	
Color	Orange
Luminous Intensity Min	8
Luminous Intensity Typical	1.7
Test Current mA	20mA
Power Dissipation Max	100mW



[x597 -3xx1 -5xx Datasheet](#)

[check stock](#)



[This is a
RoHS Compliant Product
To learn more click here](#)