

Part Number: **5973302607F**

### General Description

Series	597
Configuration	1206 Package
Description	SMD LED 1206 G 7" Reel
Package Options	Tape and Reel
Lamp Type	Single Color
Lens Color	Non - Diffused

### Absolute Maximum Ratings (Ta = 25°C)

Forward Current mA	30mA
Reverse Current	100 @ Vr =4V
Forward Current Pulsed	120mA
Derating	from 50°C @ .6mA/°C
Solder Temperature	260°C for 5 sec
Operating Temperature	-55~+100
Storage Temperature	-55~+100

### Operating Characteristics

Color	Green
Luminous Intensity Min	4
Luminous Intensity Typical	8
Luminous Intensity Max	30
Test Current mA	10mA
Dominant Wavelength Typical	569nm
Power Dissipation Max	100mW



[check stock](#)



[This is a RoHS Compliant Product.](#)  
[To learn more click here.](#)