

[Home](#) > [5973403607F](#)

Search For

Part Number

Part Number: **5973403607F**

General Description

Series	597
Configuration	1206 Package
Description	SMD LED 1206 Y 7" Reel
Package Options	Tape and Reel
Lamp Type	Single Color
Lens Color	Non - Diffused

Absolute Maximum Ratings (Ta = 25Å °)

Forward Current mA	20mA
Reverse Current	100 @ Vr =4V
Forward Current Pulsed	80mA
Derating	from 50Å° @ .4mA/Å°C
Solder Temperature	260Å° for 5 sec
Operating Temperature	-55 - +85
Storage Temperature	-55 - +85

Operating Characteristics

Color	Yellow
Luminous Intensity Min	25
Luminous Intensity Typical	50
Test Current mA	-
Dominant Wavelength Typical	588
Power Dissipation Max	60mW



5973403607F

[check stock](#)



[This is a RoHS Compliant Product](#)
[To learn more click here](#)