

Part Number: **5219201**

General Description	
Series	521
Configuration	5 mm Lens
Description	Discrete LED Lamp
Package Options	Bulk Packaging
Sizes	5mm
Lamp Type	Single Color
Lens Color	Tinted Non -Diff

Absolute Maximum Ratings (Ta = 25Â°)	
Forward Current mA	30mA
Reverse Current	100 @ Vr = 5V
Forward Current Pulsed	120mA
Derating	from 50Â° @ .4mA/Â°C
Solder Temperature	260Â° for 5 sec
Operating Temperature	-55~+100
Storage Temperature	-55~+100

Operating Characteristics	
Color	Green
Luminous Intensity Min	19
Luminous Intensity Typical	60
Test Current mA	20mA
Dominant Wavelength Typical	569nm
Power Dissipation Max	100mW



[check stock](#)