

[Request more info](#)

Part Number : 5505607100F






This is a  
RoHS Compliant Product  
[To learn more click here](#)

## General Description

Series	550
Configuration	5 mm Lens
Description	5 mm CBI
Package Options	Bulk Packaging
Sizes	5mm
Lamp Type	Single Color
Viewing	Right Angle
Polarity	Cathode Right
Lens Style	Non-Diffused
LED Centerline	3.00

## Absolute Maximum Ratings (Ta = 25°)

Forward Current mA	30mA
Derating	from 25° @ 1.8 mW/°C
Solder Temperature	260° for 5 sec
Operating Temperature	-20 to +100
Storage Temperature	-55 to +100

## Operating Characteristics

LED Type	High Efficiency
Color	Green
Luminous Intensity Min	80
Luminous Intensity Typical	120
Test Current mA	20mA
Emitted Color	Green
Power Dissipation Max	135mW