



- Circuit Board Indicators
- Panel Mount Indicators
- Solid State Lighting
- Traffic Signals
- Vehicle Lighting
- Rail
- Obstruction Lighting
- Hazardous Area Lighting
- Heliport Lighting

how to purchase

-  sales contacts
-  stock check

search

Product Line Search

Please select a Product Line to search.

Circuit Board Indicators

find

Part # / Text Search

Part No.:

Text Search:

search

quick links

Dialight Corporate Video


Presentation at LightFair 2007 - "Presentation of White LEDs" : by Ian Ferguson, Georgia Tech in conjunction with Dialight Corp. [View PDF File](#)

Application Notes
FAQs

Dialight Ltd (UK)
Dialight Garufo
Dialight BLP
LumiDrives

Circuit Board Indicators - Through Hole Indicators		
P/N# 5530203200F	3 mm Lens	
Description	3 mm Bi-Level CBI	
Package Options	50 Pieces Per Bag	
Product Type	Through Hole Indicators	
Sub Product Type	with Bi-Level Housing	
Configuration	3 mm Lens	
Viewing	Right Angle	
Viewing Angle	60	
Test Current (mA)	2mA	

Absolute Maximum Ratings (Ta = 25 °)	
Solder Temp	260Å° for 5 sec
Operating Temp	-40 to + 100° C
Storage Temp	-55 to +100° C



Operating Characteristics			
LED Position	Found in position(s): 1	Found in position(s): 2	
Color	Blank	Yellow	
Lamp Type	Single Color	Single Color	
LED Type		Low Current	
Intensity Min (mcd)		2.3	
Intensity Typ (mcd)		5.0	
Intensity Max (mcd)			
Fwd Voltage Min			
Fwd Voltage Typ			
Fwd Voltage Max			
Dom Wavelength Min (nm)			
Dom Wavelength Typ (nm)			
Dom Wavelength Max (nm)			
Power Dissipation Max (mW)		75	
Backlighting			
Pitch Between Vertical			
Pitch Between Horizontal			
Lum Intensity Min			
Lum Intensity Typ			
Lum Intensity Max			

Distributor Stock Check

Check stock with our distributors now.

5530203200F

check stock