



Circuit Board Indicators

Panel Mount Indicators

Solid State Lighting

Traffic Signals

Vehicle Lighting

Rail

Obstruction Lighting

Hazardous Area Lighting

Heliport Lighting

how to purchase

sales contacts

stock check

search

Product Line Search

Please select a Product Line to search.

Circuit Board Indicators

find

Part # / Text Search

Part No.:

Text Search:

search

quick links

Dialight Corporate Video

Presentation at LightFair 2007 - "Presentation of White LEDs" : by Ian Ferguson, Georgia Tech in conjunction with Dialight Corp. View PDF File

Application Notes

FAQs

Dialight Ltd (UK)

Dialight Garufo

Dialight BLP

LumiDrives

Circuit Board Indicators - Through Hole Indicators

P/N# 5530323200F3 mm Lens

Description

Package Options

Product Type

Sub Product Type

Configuration

Viewing

Viewing Angle

Test Current (mA)

3 mm Bi-Level CBI

50 Pieces Per Bag

Through Hole Indicators

with Bi-Level Housing

3 mm Lens

Right Angle

60

5V

Absolute Maximum Ratings

(Ta = 25 °)

Solder Temp

Operating Temp

Storage Temp

260Å° for 5 sec

-40 to +85° C

-55 to +100° C

RoHS /pB Free

view PDF

Operating Characteristics

LED Position	Found in position(s): 1	Found in position(s): 2
Color	Green	Yellow
Lamp Type	Single Color	Single Color
LED Type	Integral Resistor	Integral Resistor
Intensity Min (mcd)	5.6	3.7
Intensity Typ (mcd)	19.0	12.6
Intensity Max (mcd)		
Fwd Voltage Min		
Fwd Voltage Typ		
Fwd Voltage Max		
Dom Wavelength Min (nm)		
Dom Wavelength Typ (nm)		
Dom Wavelength Max (nm)		
Power Dissipation Max (mW)		
Backlighting		
Pitch Between Vertical		
Pitch Between Horizontal		
Lum Intensity Min		
Lum Intensity Typ		
Lum Intensity Max		

Distributor Stock Check

Check stock with our distributors now.

5530323200F

check stock

Distributor Stock Check

Check stock with our distributors now.

5530323200F

[check stock](#)