

[Request more info](#)

Part Number : 5554008F



5554008F

 [555-4xxx Datasheet](#)
 [C17763](#)


This is a
RoHS Compliant Product
[To learn more click here](#)


General Description

Series	555
Configuration	2 mm Lens
Description	2 mm 24V Integral Resistor Quad CBI
Package Options	Bulk Packaging
Sizes	2mm
Lamp Type	Single Color
Viewing	Right Angle
Polarity	Cathode Right
Lens Style	Non-Diffused

Absolute Maximum Ratings (Ta = 25°)

Solder Temperature	260° for 5 sec
Operating Temperature	-40 to +85
Storage Temperature	-55 to +100

Operating Characteristics

Color	Red 
Luminous Intensity Min	0.4
Luminous Intensity Typical	0.9
Test Current mA	24V
Emitted Color	Red