





[Request more info](#)

Part Number : 5580701007F



5580701007F

[Check Stock](#)

-  [558 Series IGS](#)
-  [558 Series STP](#)
-  [5580101007F Detailed Spec](#)
-  [558 Series LED Panel Mount Indicators Datasheet](#)



This is a
RoHS Compliant Product
[To learn more click here](#)

General Description

Series	558
Configuration	Daylight Viewable Snap-In PMI
Description	Red Snap-In LED Panel Mount Indicator
Housing	Black PBT; UL 94V-0
Keywords	Daylight
LED Type	Ultra Bright
Color	Red 
Mounting Method	Snap In
Compliance	Daylight-Front of Panel, UL94V-0
Termination	26 AWG 14" Wire Lead
Mounting Hole Size	.156"
Panel Thickness	.062"
Lens Style	Non-Tinted
Diffused	Non-Diffused
Luminous Intensity Typical	170
Forward Current mA	40 mA
Voltage	12.0 VDC
Operating Temperature	-55 +100
Storage Temperature	-55 +100