



- [Circuit Board Indicators](#)
- [Panel Mount Indicators](#)
- [Solid State Lighting](#)
- [Traffic Signals](#)
- [Vehicle Lighting](#)
- [Rail](#)
- [Obstruction Lighting](#)
- [Hazardous Area Lighting](#)
- [Heliport Lighting](#)

how to purchase

- [sales contacts](#)
- [stock check](#)

search

Product Line Search

Please select a Product Line to search.

Circuit Board Indicators

find

Part # / Text Search

Part No.:

Text Search:

search

quick links

Dialight Corporate Video


Presentation at LightFair 2007 - "Presentation of White LEDs" : by Ian Ferguson, Georgia Tech in conjunction with Dialight Corp. [View PDF File](#)

Application Notes  
FAQs

Dialight Ltd (UK)  
Dialight Garufo  
Dialight BLP  
LumiDrives

Circuit Board Indicators - Through Hole Indicators	
P/N# 5600207F	Bi-Pin LED Lamp Single Color
Description	Bi Pin LED Lamp
Package Options	25 Pieces Per Bag
Product Type	Through Hole Indicators
Sub Product Type	Discrete LED
Configuration	Bi-Pin LED Lamp
Lamp Type	Single Color
Viewing	Top View
Viewing Angle	50

Absolute Maximum Ratings (Ta = 25 °)	
Operating Temp	-55 to +100° C
Storage Temp	-55 to +100° C



Operating Characteristics

LED Position	
Color	Green
Lamp Type	Single Color
LED Type	Resistor
Intensity Min (mcd)	
Intensity Typ (mcd)	5.8
Intensity Max (mcd)	
Fwd Voltage Min	
Fwd Voltage Typ	
Fwd Voltage Max	
Dom Wavelength Min (nm)	570
Dom Wavelength Typ (nm)	
Dom Wavelength Max (nm)	
Power Dissipation Max (mW)	
Backlighting	
Pitch Between Vertical	
Pitch Between Horizontal	
Lum Intensity Min	
Lum Intensity Typ	
Lum Intensity Max	

Distributor Stock Check

Check stock with our distributors now.

5600207F

check stock