



- Circuit Board Indicators
- Panel Mount Indicators
- Solid State Lighting
- Traffic Signals
- Vehicle Lighting
- Rail
- Obstruction Lighting
- Hazardous Area Lighting
- Heliport Lighting

how to purchase

-  [sales contacts](#)
-  [stock check](#)

 [search](#)

Product Line Search

Please select a Product Line to search.

Circuit Board Indicators 

[find](#) 

Part # / Text Search

Part No.:

Text Search:

[search](#) 

quick links

Dialight Corporate Video

Presentation at LightFair 2007 - "Presentation of White LEDs" : by Ian Ferguson, Georgia Tech in conjunction with Dialight Corp. [View PDF File](#)

Application Notes FAQs

Dialight Ltd (UK)
Dialight Garufo
Dialight BLP
LumiDrives

Circuit Board Indicators - Through Hole Indicators

P/N# **5600606F**

Bi-Pin LED Lamp Single Color

Description	Bi Pin LED Lamp
Package Options	25 Pieces Per Bag
Product Type	Through Hole Indicators
Sub Product Type	Discrete LED
Configuration	Bi-Pin LED Lamp
Lamp Type	Single Color
Viewing	Top View
Viewing Angle	35

Absolute Maximum Ratings (Ta = 25 °)

Operating Temp	-55 to +100° C
Storage Temp	-55 to +100° C



RoHS / pB Free
[view PDF](#)

Distributor Stock Check

Check stock with our distributors now.

5600606F

[check stock](#) 

Operating Characteristics

LED Position	
Color	Yellow
Lamp Type	Single Color
LED Type	Resistor
Intensity Min (mcd)	
Intensity Typ (mcd)	90.0
Intensity Max (mcd)	
Fwd Voltage Min	
Fwd Voltage Typ	
Fwd Voltage Max	
Dom Wavelength Min (nm)	588
Dom Wavelength Typ (nm)	
Dom Wavelength Max (nm)	
Power Dissipation Max (mW)	
Backlighting	
Pitch Between Vertical	
Pitch Between Horizontal	
Lum Intensity Min	
Lum Intensity Typ	
Lum Intensity Max	