

[Request more info](#)
**Part Number : 5615401070F**




### General Description

Series	561
Configuration	5 mm Lens
Description	5 mm Stand-Off 0.700" Amb
Package Options	Bulk Packaging
Sizes	5mm
Lamp Type	Single Color
Color	Amber
Viewing	Top View
Polarity	Cathode Right
Lens Style	Diffused

### Absolute Maximum Ratings (Ta = 25°)

Forward Current mA	25mA
Derating	from 50° @ .5 mA/°C
Solder Temperature	260° for 5 sec
Operating Temperature	-25 to +85
Storage Temperature	-30 to +100

### Operating Characteristics

#### COLORTAGHERE

LED Type	High Efficiency
Luminous Intensity Min	17
Luminous Intensity Typical	34
Test Current mA	20mA
Emitted Color	Amber
Power Dissipation Max	75mW



This is a  
RoHS Compliant Product  
[To learn more click here](#)