

[Request more info](#)

Part Number : 5615801060F



General Description

Series	561
Configuration	5 mm Lens
Description	5 mm Stand-Off 0,600" Amb WC
Package Options	Bulk Packaging
Sizes	5mm
Lamp Type	Single Color
Color	Amber
Viewing	Top View
Polarity	Cathode Right
Lens Style	Non-Diffused

Absolute Maximum Ratings (Ta = 25°)

Solder Temperature	260° for 5 sec
Operating Temperature	-30 to +100
Storage Temperature	-30 to +100

Operating Characteristics

COLORTAGHERE

LED Type	High Efficiency
Luminous Intensity Min	60
Luminous Intensity Typical	90
Test Current mA	20mA
Emitted Color	Amber
Power Dissipation Max	125mW



This is a
RoHS Compliant Product
[To learn more click here](#)