



Circuit Board Indicators

Panel Mount Indicators

Solid State Lighting

Traffic Signals

Vehicle Lighting

Rail

Obstruction Lighting

Hazardous Area Lighting

Heliport Lighting

how to purchase

sales contacts

stock check

search

Product Line Search

Please select a Product Line to search.

Circuit Board Indicators

find

Part # / Text Search

Part No.:

Text Search:

search

quick links

Dialight Corporate Video

Presentation at LightFair 2007 - "Presentation of White LEDs" : by Ian Ferguson, Georgia Tech in conjunction with Dialight Corp. View PDF File

Application Notes

FAQs

Dialight Ltd (UK)

Dialight Garufo

Dialight BLP

LumiDrives

Circuit Board Indicators - Through Hole Indicators

P/N# 5680121233F

Rectangle Lens

Description

Package Options

Product Type

Sub Product Type

Configuration

Viewing

Viewing Angle

Test Current (mA)

2X4 mm Quad-Level CBI R-G-Y-Y

5 Pieces Per Bag

Through Hole Indicators

with Quad Level Housing

Rectangle Lens

Right Angle

104

10mA

Absolute Maximum Ratings

(Ta = 25 °)

Solder Temp

Operating Temp

Storage Temp

260Å° for 5 sec

-55 to +100° C

-55 to +100° C

RoHS /pB Free

view PDF

Operating Characteristics

LED Position	Found in position(s): 1	Found in position(s): 2	Found in position(s): 3,4
Color	Red	Green	Yellow
Lamp Type	Single Color	Single Color	Single Color
LED Type	High Efficiency	High Efficiency	High Efficiency
Intensity Min (mcd)	1.1	0.0	0.0
Intensity Typ (mcd)	3.7		
Intensity Max (mcd)			
Fwd Voltage Min			
Fwd Voltage Typ			
Fwd Voltage Max			
Dom Wavelength Min (nm)	566	566	566
Dom Wavelength Typ (nm)			
Dom Wavelength Max (nm)			
Power Dissipation Max (mW)	100	100	60
Backlighting			
Pitch Between Vertical			
Pitch Between Horizontal			
Lum Intensity Min			
Lum Intensity Typ			
Lum Intensity Max			

Distributor Stock Check

Check stock with our distributors now.

5680121233F

check stock

Distributor Stock Check

Check stock with our distributors now.

5680121233F

[check stock](#)