



Product Navigation

- Home
- About Us
- Products
- Investor Relations
- News
- Contact Us
- Secure EAX

Circuit Board Indicators

Panel Mount Indicators

Solid State Lighting

Traffic Signals

Vehicle Lighting

Rail

Obstruction Lighting

Hazardous Area Lighting

Heliport Lighting

how to purchase

sales contacts

stock check

search

Product Line Search

Please select a Product Line to search.

Circuit Board Indicators

find

Part # / Text Search

Part No.:

Text Search:

search

quick links

Dialight Corporate Video

Presentation at LightFair 2007 - "Presentation of White LEDs" : by Ian Ferguson, Georgia Tech in conjunction with Dialight Corp. [View PDF File](#)

Application Notes
FAQs

Dialight Ltd (UK)
Dialight Garufo
Dialight BLP
LumiDrives

Circuit Board Indicators - Through Hole Indicators

P/N# 5682211023F

3 mm Lens

Description	3 mm Quad-Level CBI R-X-G-Y
Package Options	5 Pieces Per Bag
Product Type	Through Hole Indicators
Sub Product Type	with Quad Level Housing
Configuration	3 mm Lens
Viewing	Right Angle
Viewing Angle	45
Test Current (mA)	10mA

Absolute Maximum Ratings (Ta = 25 °)



RoHS /pB Free
view PDF

Distributor Stock Check

Check stock with our distributors now.

5682211023F

check stock

Operating Characteristics

LED Position	Found in position(s): 1	Found in position(s): 2	Found in position(s): 3	Found in position(s): 4
Color	Red	Blank	Green	Yellow
Lamp Type	Single Color	Single Color	Single Color	Single Color
LED Type	High Efficiency		High Efficiency	High Efficiency
Intensity Min (mcd)	8.7		32.0	10.0
Intensity Typ (mcd)	29.0		50.0	
Intensity Max (mcd)				50
Fwd Voltage Min				
Fwd Voltage Typ				
Fwd Voltage Max				
Dom Wavelength Min (nm)				
Dom Wavelength Typ (nm)				
Dom Wavelength Max (nm)				
Power Dissipation Max (mW)	100		100	60
Backlighting				
Pitch Between Vertical				
Pitch Between Horizontal				
Lum Intensity Min				
Lum Intensity Typ				
Lum Intensity Max				