



Product Navigation

Circuit Board Indicators

Panel Mount Indicators

Solid State Lighting

Traffic Signals

Vehicle Lighting

Rail

Obstruction Lighting

Hazardous Area Lighting

Heliport Lighting

how to purchase

sales contacts

stock check

search

Product Line Search

Please select a Product Line to search.

Circuit Board Indicators

find

Part # / Text Search

Part No.:

Text Search:

search

quick links

Dialight Corporate Video

Presentation at LightFair 2007 - "Presentation of White LEDs" : by Ian Ferguson, Georgia Tech in conjunction with Dialight Corp. [View PDF File](#)

Application Notes
FAQs


Dialight Ltd (UK)
Dialight Garufo
Dialight BLP
LumiDrives

Circuit Board Indicators - Through Hole Indicators

P/N# 5682212239F	3 mm Lens
Description	3 mm Backlighting Quad-Level CBI G-G-Y-B
Package Options	5 Pieces Per Bag
Product Type	Through Hole Indicators
Sub Product Type	with Quad Level Housing
Configuration	3 mm Lens
Viewing	Right Angle
Viewing Angle	45
Test Current (mA)	10mA

Absolute Maximum Ratings (Ta = 25 °)

Solder Temp	260Å° for 5 sec
Operating Temp	-55 to +100° C
Storage Temp	-55 to +100° C



Distributor Stock Check

Check stock with our distributors now.

5682212239F

[check stock](#)

Operating Characteristics

LED Position	Found in position(s): 1,2	Found in position(s): 3	Found in position(s): 4
Color	Green	Yellow	Blue
Lamp Type	Single Color	Single Color	Single Color
LED Type	High Efficiency	High Efficiency	High Efficiency
Intensity Min (mcd)	32.0	10.0	7.1
Intensity Typ (mcd)	50.0		12.5
Intensity Max (mcd)		50	18
Fwd Voltage Min			
Fwd Voltage Typ			
Fwd Voltage Max			
Dom Wavelength Min (nm)			
Dom Wavelength Typ (nm)			
Dom Wavelength Max (nm)			
Power Dissipation Max (mW)	100	60	90
Backlighting			
Pitch Between Vertical			
Pitch Between Horizontal			
Lum Intensity Min			
Lum Intensity Typ			
Lum Intensity Max			