



Product Navigation Circuit Board Indicators Panel Mount Indicators Solid State Lighting Traffic Signals Vehicle Lighting Rail Obstruction Lighting Hazardous Area Lighting Heliport Lighting how to purchase sales contacts stock check search Product Line Search Please select a Product Line to search. Circuit Board Indicators find Part # / Text Search Part No.: Text Search: search quick links Dialight Corporate Video Presentation at LightFair 2007 - "Presentation of White LEDs" : by Ian Ferguson, Georgia Tech in conjunction with Dialight Corp. View PDF File Application Notes FAQs Dialight Ltd (UK) Dialight Garufo Dialight BLP LumiDrives	Circuit Board Indicators - Through Hole Indicators P/N# 5692211100F 3 mm Lens Single Color Description Package Options Product Type Sub Product Type Configuration Lamp Type Viewing Viewing Angle Test Current (mA) Forward Current (mA) LED Centerline Polarity 3 mm Bi-Level CBI R-R 50 Pieces Per Bag Through Hole Indicators with Bi-Level Housing 3 mm Lens Single Color Right Angle 45 10mA 30mA 2.29 Cathode Pin 1 & 3 Absolute Maximum Ratings (Ta = 25 °) Derating Reverse Voltage Solder Temp Operating Temp Storage Temp from 50Â° @ .4 mA/Â°C 5 V 260Â° for 5 sec -55 to +100° C -55 to +100° C RoHS /pB Free view PDF Operating Characteristics LED Position Color Lamp Type LED Type Intensity Min (mcd) Intensity Typ (mcd) Intensity Max (mcd) Fwd Voltage Min Fwd Voltage Typ Fwd Voltage Max Dom Wavelength Min (nm) Dom Wavelength Typ (nm) Dom Wavelength Max (nm) Power Dissipation Max (mW) Backlighting Pitch Between Vertical Pitch Between Horizontal Lum Intensity Min Lum Intensity Typ Lum Intensity Max 1,2 Red Single Color High Efficiency 8.7 29.0 100 4.57
---	---