


Dialight - Leader in LED Technology



- ? [Circuit Board Indicators](#)
- ? [Panel Mount Indicators](#)
- ? [Solid State Lighting](#)
- ? [Traffic Signals](#)
- ? [Vehicle Lighting](#)
- ? [Rail](#)
- ? [Obstruction Lighting](#)
- ? [Hazardous Area Lighting](#)
- ? [Heliport Lighting](#)

| Circuit Board Indicators - Surface Mount Indicators | |
|---|---------------------|
| P/N# | PLCC-2 Single Color |
| 5973904307F | |
| Description | |

Region:

Product Line:

Circuit Board Indicators

| | |
|----------------------------|---------------------|
| Forward Current Continuous | 30 mA |
| Forward Current Pulse | 90 mA |
| Derating | from 40° @ .42mA/°C |
| Solder Temp | 240° for 20 sec |
| Operating Temp | -40~+100° C |
| Storage Temp | -40~+100° C |

Distributor Stock Check

Check stock with our distributors now.

5973904307F



Check stock with our distributors now.

RoHS Compliant Product

5973904307F

Please note that the stock check is **only applicable** to products *within* **Circuit Board Indicators** and **Panel Mount Indicators**.

Please select a Product Line to search.

Circuit Board Indicators

Part No.:

Text Search:

| Operating Characteristics | |
|----------------------------|--------------|
| LED Position | |
| Color | White |
| Lamp Type | Single Color |
| LED Type | InGaN |
| Intensity Min (mcd) | 224 |
| Intensity Typ (mcd) | 285.0 |
| Intensity Max (mcd) | 450.0 |
| Fwd Voltage Min | 3.9 |
| Fwd Voltage Typ | 4.3 |
| Fwd Voltage Max | |
| Dom Wavelength Min (nm) | |
| Dom Wavelength Typ (nm) | 114 |
| Dom Wavelength Max (nm) | |
| Power Dissipation Max (mW) | |
| Backlighting | |
| Pitch Between Vertical | |
| Pitch Between Horizontal | |
| Lum Intensity Min | |
| Lum Intensity Typ | |
| Lum Intensity Max | |

Copyright 2006 Dialight. All rights reserved | [Privacy Policy](#)

[Dialight Corporate Video](#)

Presentation at LightFair 2007 - "Presentation of White LEDs" : by Ian Ferguson, Georgia Tech in conjunction with Dialight Corp. [View PDF File](#)

[Application Notes](#)
[FAQs](#)

[Dialight Ltd \(UK\)](#)
[Dialight Garufo](#)
[Dialight BLP](#)
[LumiDrives](#)