

Search For 

Home> 5973604307F

Part Number: **5973604307F****General Description**

Series	597
Configuration	PLCC -2
Description	SMD LED PLCC BL InGaN 7" Reel
Package Options	Tape and Reel
Lamp Type	Single Color
LED Type	InGaN
Lens Color	Non - Diffused

Absolute Maximum Ratings (Ta = 25Å °)

Forward Current mA	30mA
Forward Current Pulsed	100mA
Derating	from 40Å° @ .42mA/Å°C
Solder Temperature	240Å° for 20 sec
Operating Temperature	-55~+100
Storage Temperature	-55~+100

Operating Characteristics

Color	Blue
Luminous Intensity Min	45
Luminous Intensity Typical	56
Test Current mA	20mA
Dominant Wavelength Typical	470nm
Power Dissipation Max	14mW

[check stock](#) 

This is a
RoHS Compliant Product
To learn more click here