






P.C.B LAYOUT



▲ CIRCUIT: SPST



NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
3. TERMINAL NUMBERS FOR REF. ONLY
4. CONTACT RATING: 50mA @ 12VDC
5. TRAVEL: 0.30 ± 0.15 mm
- ▲ 6. OPERATING FORCE: 260 ± 50 gf
7. CONTACT RESISTANCE: $100\text{m}\Omega$ MAX.
8. ELECTRICAL LIFE: 100,000 CYCLES
9. ▲ DENOTES CRITICAL PARAMETER
10. CONTACT MATERIAL: SILVER

REV	ECO NO	DESCRIPTION	DATE	BY	E-SWITCH®				OBJECT ID
B	ECO-102067	PRINT UPDATE	08/11/23	JS	TITLE TL1100EF260Q				000017206
					SCALE	DATE	DR	DWG	REV
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED					2:1	4/21/1997	MM	P001104	B