



Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)


EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: FEB 2026 (253) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts







TE Part # 494615-E
SMCB 12 F AB VV 7-13 CL * H007 137 E002



TE Part # 364743-E
SMCB 12 F AB VV 7-13 CL * H007 137 E001




TE Part # 154740-E
SMCQ 12 F AB VV 7-03 CL * 0007 137 E002




TE Part # 354939-E
SMCQ 12 F AB VV 7-03 CL * 0007 137 E002




TE Part # 044663-E
SMCB 12 F AB VV 3-01 * * 0005 137 POS 05




TE Part # 254262-E
SMCQ 12 F AB VV 7-03 CL * 0007 137 E002




TE Part # 494222-E
SMCQ 12 F AB VV 7-03 CL * 0007 137 E002



TE Part # 335042-E
SMCQ 12 F AB VV 7-03 CL * 0007 137 E002




TE Part # 234198-E
SMCB 12 F AB VV 7-23 CL * H007 137 E002




TE Part # 394958-E
SMCB 12 F AB VV 7-13 CL * H007 107 E003




TE Part # 214345-E
SMCB 12 F AB VV 6-01 VH * 0008 137 E002




TE Part # 494543-E
SMCB 12 F AB VV 7-23 CL * 9999 137 E002




TE Part # 154717-E
SMCB 12 F AB VV 7-03 CL * H007 137 E002



TE Part # 154805-E
SMCB 12 F AB VV 7-13 CL * H007 137 E002



TE Part # 534362-E
SMCQ 12 F AB VV 7-03 CL * 0007 137 E002



TE Part # 494616-E
SMCB 12 F AB VV 7-23 CL * H007 137 E002

Documents

- CAD Files

Customer View Model

[ENG_CVM_CVM_364742-E_C.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_364742-E_C.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_364742-E_C.3d_stp.zip](#)

English



3D PDF

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Product Specification

English

Product Specification

English