



A
B
C
D
E
F


A
B
C
D
E




Stecklänge / mating length



E = early mate, late break / voreilend
S = standard
L = late mate, early break / nacheilend




Bestückungsplan / contact layout



Lötanschluss 0,6x0,6mm / solder terminal 0,6x0,6mm
Isolierwerkstoff / housing material : PBT GF 30
Bauart 4 / type 4
Anforderungsstufe 1 = 500 Steckzyklen / performance class 1 = 500 mating cycles
Fehlende Maße und Angaben nach IEC 60 603-2 / DIN EN 60 603-2
Missing information and dimensions per IEC 60 603-2 / DIN EN 60 603-2

Leiterplatten-Lochbild / PCB drillhole pattern



Weitergabe sowie Vervielfältigung dieses Dokuments, Verwertung und Mitteilung seines Inhalts sind verboten, soweit nicht ausdrücklich gestattet. Zuwiderhandlungen verpflichten zu Schadenersatz. Alle Rechte für den Fall der Patent-, Gebrauchsmuster- oder Geschmacksausbeuteeintragung vorbehalten. The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited. Offenders will be held liable for the payment of damages. All rights reserved in the event of the grant of a patent, utility model or design. Die deutsche Version dieser Zeichnung dient nur zur Erleichterung der Handhabung. Bei Abweichungen von dem englischen Original gilt das englische Original. The german version of this drawing has been offered for convenience only and may deviate from the english original. In case of any deviation the English version shall prevail.

| | | | | |
|--|--|--------------------------|---|---------|
| Dimension no. | Tolerances | All Dimensions in mm | Scale | 2:1 |
| | ISO 8015 | | Material | |
| Customer drawing: | Subject to modification without prior notice. Drawing will not be updated. | | Messerleiste C 64 Löt Male Connector C64 solder C-384046 | |
| This Drawing is a controlled Document. | | | | |
| 1 | 17.03.2023 | | Class | STVC |
| Index | Date | | | 1 A3 |