




Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: FEB 2026 (253) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Bromine/Chlorine - Br and Cl < 900 ppm per homogenous material. Also BFR /CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 454587-E
SRCBUG A 2,54 2 2 CSI 046 E1 ADV J 2 324

Customers Also Bought



TE Part #384474-E
SRCA 2,54 4 M 1 SMD 137 E1 168 * GURT *



TE Part #384472-E
SRCA 2,54 4 M 1 SMD 137 E1 166 * GURT *



TE Part #384465-E
SRCP 2,54 4 M 1 SMD 137 E1 168 * GU-H *



TE Part #504285-E
MCBA 8 M * SMD 137 * 176 * GURT * J 2 50



TE Part #504255-E
MCBA 4 M * SMD 137 * 176 * GURT * J 2 50



TE Part #234832-E
SRCA 2,54 2 M 1 SMD 137 E1 094 * GURT *



TE Part #284123-E
SRCA 2,54 8 M 1 SMD 137 E1 167 * GURT *



TE Part #284122-E
SRCA 2,54 8 M 1 SMD 137 E1 166 * GURT *



TE Part #454193-E
SRCA 2,54 4 M 1 SMD 137 E1 105 * GURT *



TE Part #515406-E
SRCA 2,54 2 M 1 SMD 137 E1 168 * GURT 99

Documents

Product Drawings

SRCA 2,54 2 M 1 SMD 137 E1 105 * GURT *

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_454189-E_G.3d_igs.zip



English

Customer View Model

[ENG_CVM_CVM_454189-E_G.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_454189-E_G.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[MaxiBridge - Receptacle & Header](#)

English