

Datasheet

Art.No. 02.125.3029.8

Female contact D 3,6- 2,5 QMM AG

Female contact, turned Ø 3,6 mm, 2,5 mm², AWG 14, Ag



Art.No.	02.125.3029.8
EAN	4015573681750
Order unit	100 pieces

Approvals

Technical data

General

Model	Bus connection
Wire strip length	10 mm
Min. conductor cross section flexible wire	2.5
Max. conductor cross section flexible wire	2.5
Min. UL/CSA wire diameter flexible wire	14 AWG
Max. UL/CSA wire diameter flexible wire	14 AWG
Mating cycles	500
Connection type	Crimp
Material	Other
Massive contact	Yes
Contact pin diameter	3.6 mm
Surface	Silver-plated
Inflammability class of insulation material acc. with UL94	Other
Contact resistance	1 mOhm

