

Datasheet

Item No. 70.333.2435.0

Bottom BAS GUT GD 24 M25 50 A0

revos BASIC 500V size 24 closed-bottom base with cable gland M25, bottom, double locking lever



Item No.	70.333.2435.0
EAN	4015573618695
order unit	1 Piece(s)

Approvals



Technical data

General

Nominal voltage	500
Housing material	Aluminium
Colour	Grey
Surface	With powder coating
Degree of protection (IP)	IP54
UV resistant	Yes
Inflammability class of insulation material acc. with UL94	Other
Operating temperature range min.	-40 °C
Operating temperature range max.	120 °C

Model

DIN-size	24
Model	Surface mounting (base)
Locking mechanism	Double locking levers
Cable entry	Below
Type of cable	Gland nut
With cable screw gland	Yes
Thread size M	25
Hinged lid	No
EMC-version	No

Drawings

Ausführung .0
version .0

Further data see catalog
further data see catalog

Teile-Nr. part number	TYP type	Ausführung version
70.333.2435.0	BAS GUT GD 24 M25 50 A0	Kabelverschraubung/ cable gland M25
70.333.2435.1	BAS GUT GD 24 M25 50 A1	Gewinde / thread M25

Fräsen/rough		2007	03.06.	Schnitt 1.	70.333.2435.0 01K
General tolerance		Made in mm/Dimensions are in mm			
Index		GEHAUSEUNTERTEIL			
Änderung/Revision		geschlossen; Größe 24; Union M 25 closed-bottom bases; cable gland bottom; size 24			